



Ultrasonic cleaning unit Elmasonic Xtra, Type: 12



Order data

Order number	082006 12
GTIN	4250004112544
Item class	04S

Description

Version:

Powerful ultrasonic cleaning by the Elmasonic xtra series for heavy-duty applications.

- **Greater ultrasonic effect due to automatic dynamic function.**
- **Selectable Eco mode for gentle cleaning and energy savings.**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**
- **Automatic safety shutdown.**

Note:

Further sizes and types on request. The suitable component basket can be found under No. 082101. Ultrasonic cleaning agent and anti-corrosion agent can be found under No. 088015 – No. 088019.

Technical description

Manufacturer's designation	Xtra 120
Length of component basket	245 mm
Cleaning bath height	190 mm
Recommended working volume	12.1 l
Item length	500 mm
Weight	11.3 kg

Data sheet

Volume	14.2 l
Item width	315 mm
Maximum ultrasonic power	880 W
Nominal voltage	220 - 240 V
Heating power	800 W
Width of component basket	195 mm
Type of product	Ultrasonic cleaning unit