



Ultrasonic cleaning unit Elmasonic Xtra, Type: 18



Order data

Order number	082006 18
GTIN	4250004112551
Item class	04S

Description

Version:

Powerful ultrasonic cleaning by the Elmasonic xtra series for heavy-duty applications.

- **Greater ultrasonic effect due to automatic dynamic function.**
- **Selectable Eco mode for gentle cleaning and energy savings.**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**
- **Automatic safety shutdown.**

Note:

Further sizes and types on request. The suitable component basket can be found under No. 082101. Ultrasonic cleaning agent and anti-corrosion agent can be found under No. 088015 – No. 088019.

Technical description

Weight	13.2 kg
Maximum ultrasonic power	1040 W
Width of component basket	255 mm
Heating power	1000 W
Manufacturer's designation	Xtra 180
Item length	530 mm
Nominal voltage	220 - 240 V

Data sheet

Recommended working volume	16.7 l
Volume	19.7 l
Item width	380 mm
Cleaning bath height	190 mm
Length of component basket	275 mm
Type of product	Ultrasonic cleaning unit