

Garant**Electronic light metal spirit level, Length: 400mm****Order data**

Order number	467520 400
GTIN	4007368121701
Item class	41H

Description**Version:**

Electronically measures the angle and displays it digitally. The measuring computer can be calibrated both horizontally and vertically in mere seconds. Can also be used conventionally thanks to one horizontal and one vertical level.

Advantage:

- **Lithium-ion battery can be charged via USB-C.**
- **Automatic screen rotation.**
- **Sturdy anodised aluminium profile.**
- **Prismatic measuring face.**
- **Acoustic guidance.**
- **Dustproof and waterproof.**
- **Integrated digital inclinometer.**

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Rechargeable battery supplied. In a stable, transparent plastic screw tube.

Optional extras:

- **USB charger No. 081601 size HC105.**
- **USB charging cable No. 081603 size USB#C.**

Technical description

Power supply	Battery-powered
--------------	-----------------

Error limit in normal position and for measurement reversal	0.5 mm/m
Error limit of electronics module	0.05 (0°; 90°); 0.1 (1° – 89°) degrees
IP Index of Protection	IP 67
Length	400 mm
Measurement technology	digital
Material of the housing	Aluminium
Calibration	H2
Type of product	Spirit level

Suitable products

No Shop URL available for: 467520 400