



Lace-up boots brown NIKOLAS XXB Mid ESD, S3S, EU shoe size: 40



Order data

Order number	092234 40
GTIN	4030839333990
Item class	09P

Description

Version:

Modern business safety boot, fits perfectly with the business outfit. Sole core of high-tech Infinergy® material from BASF for shock absorption over the entire sole.

- **Uppers of hard-wearing cowhide.**
- **Breathable leather lining.**
- **ESD-capable soft fleece inner sole.**
- **Sportive ESD full-size insole.**
- **WELLMAXX BUSINESS TPU/PU sole.**
- **ESD security.**

Standard:

EN ISO 20345:2011 S3S SRA.

Inlay provision design type tested to DGUV regulations 191.

Note:

Stock goods in EU sizes 40 – 46, can be ordered in EU sizes 40 – 48.

Technical description

EU shoe size	40
Series	NIKOLAS

Data sheet

Puncture resistance	Textile
Colour	brown
Protection class	S3S
Gender	Gentlemen's
Standard	Inlay type-tested according to DGUV regulation 191
Material of protective toe-cap	Steel
Characteristics	resistant to fuel
electrostatic characteristic	EGB/ESD
Type of product	Boots