



Lace-up boots brown NIKOLAS XXB Mid ESD, S3S, EU shoe size: 44



Order data

Order number	092234 44
GTIN	4030839334034
Item class	09P

Description

Version:

Modern business safety boot, fits perfectly with the business outfit. Sole core of high-tech Infinergy® material from BASF for shock absorption over the entire sole.

- **Uppers of hard-wearing cowhide.**
- **Breathable leather lining.**
- **ESD-capable soft fleece inner sole.**
- **Sportive ESD full-size insole.**
- **WELLMAXX BUSINESS TPU/PU sole.**
- **ESD security.**

Standard:

EN ISO 20345:2011 S3S SRA.

Inlay provision design type tested to DGUV regulations 191.

Note:

Stock goods in EU sizes 40 – 46, can be ordered in EU sizes 40 – 48.

Technical description

Colour	brown
Series	NIKOLAS

Data sheet

Protection class	S3S
EU shoe size	44
Standard	Inlay type-tested according to DGUV regulation 191
Puncture resistance	Textile
Material of protective toe-cap	Steel
Gender	Gentlemen's
Characteristics	resistant to fuel
electrostatic characteristic	EGB/ESD
Type of product	Boots