



SCMT 120408 Set 10 pieces, Grade: HBX130



Order data

Order number	260796 HBX130
GTIN	4045197670687
Item class	22D

Description

SCMT 120408 Set of 10 pieces HBX130 Corner radius: 0.8 mm
 Grade: HBX130
 Chip breaker: MM
 Cutting depth a_p : 0.1 - 3.75 mm
 Feed f : 0.08 - 0.36 mm/rev.
 Cutting speed v_c main application: 60 - 200 m/min

Technical description

Main application	M
Cutting depth a_p	0.1 - 3.75 mm
Feed f	0.08 - 0.36 mm/rev.
Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Chip breaker	MM
Grade	HBX130

Cutting speed v_c main application	60 - 200 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SCMT 120408
Number of changes/inserts	4
Type of product	Indexable insert for turning