

Garant**CaraFin diamond polishing pad, 125×175 mm, Grit: D126µm****Order data**

Order number	557515 D126
GTIN	4069515040372
Item class	51G

Description**Version:**

CaraFin diamond polishing tools coated on one side with **mono-crystalline diamond**. The bonded diamond grit achieves significantly **higher effectiveness** than loose diamond grit in polishing pastes.

CaraFin diamond polishing pad (EVA) with **open structure**, will not clog.

Advantage:

Ancillary times for preparation and cleaning, such as are required when polishing pastes are used, are eliminated.

Of high-quality **resilient polyurethane foam**.

Application:

Handy for **contour-true finish polishing and mirror finishing** of polished surfaces on all **hard materials and non-ferrous metals**. Quick polishing thanks to free-cutting characteristics.

Suitable for wet and dry polishing.

Technical description

Grinding medium code	D
Polishing stage	Pre-polishing
Product name attribute	125×175 mm
Type of product	Polerblok

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		