

**Garant****CaraFin diamond polishing pad, 125×175 mm, Grit: D151µm****Order data**

|              |               |
|--------------|---------------|
| Order number | 557515 D151   |
| GTIN         | 4069515040389 |
| Item class   | 51G           |

**Description****Version:**

**CaraFin diamond polishing tools** coated on one side with **mono-crystalline diamond**. The bonded diamond grit achieves significantly **higher effectiveness** than loose diamond grit in polishing pastes.

CaraFin diamond polishing pad (EVA) with **open structure**, will not clog.

**Advantage:**

Ancillary times for preparation and cleaning, such as are required when polishing pastes are used, are eliminated.

Of high-quality **resilient polyurethane foam**.

**Application:**

Handy for **contour-true finish polishing and mirror finishing** of polished surfaces on all **hard materials and non-ferrous metals**. Quick polishing thanks to free-cutting characteristics.

Suitable for wet and dry polishing.

**Technical description**

|                        |               |
|------------------------|---------------|
| Polishing stage        | Pre-polishing |
| Grinding medium code   | D             |
| Product name attribute | 125×175 mm    |
| Type of product        | Polerblok     |

**User data**

|                                | <b>Suitability</b>                           | <b>V<sub>c</sub></b> | <b>ISO code</b> |
|--------------------------------|----------------------------------------------|----------------------|-----------------|
| Alu Mg                         | suitable                                     |                      |                 |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                     |                      |                 |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                     |                      |                 |
| Steel < 55 HRC                 | suitable                                     |                      |                 |
| Steel < 60 HRC                 | suitable                                     |                      |                 |
| Steel < 67 HRC                 | suitable                                     |                      |                 |
| Carbide (HM)                   | suitable                                     |                      |                 |
| INOX                           | suitable                                     |                      |                 |
| Ti                             | suitable                                     |                      |                 |
| GG(G)                          | suitable                                     |                      |                 |
| CuZn                           | suitable                                     |                      |                 |
| Plastic, GRP                   | suitable                                     |                      |                 |
| Paint                          | suitable                                     |                      |                 |
| Uni                            | suitable                                     |                      |                 |
| wet maximum                    | suitable only under<br>restricted conditions |                      |                 |
| dry                            | suitable                                     |                      |                 |