

Garant**Garment locker with cylinder lock, Number of compartments: 8****Order data**

Order number	949031 8
GTIN	4069515040457
Item class	91G

Description**Version:**

The body of the garment locker has plastic slides in the base frame and a removable plinth panel at the front. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With high quality cylinder lock in the slide handle.

Standard:

DIN 4547

Colour:

Body light grey RAL 7035, doorsanthracite RAL 7016, **powder-coated.**

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	800 mm
Standard	DIN 4547

Data sheet

usable width of each compartment	342 mm
Height	1850 mm
Lock version	Cylinder lock
Cabinet fronts	Plain sheet metal swing door
Number of compartments	8
usable height of each compartment	370 mm
Sloping roof	no
Weight	76 kg
Support cabinet version	Aluminium feet
Depth	520 mm
Nameplate	yes
Special paints available	yes
Ventilation slots in the back wall	yes
usable depth of each compartment	472 mm
Material thickness	0.9 mm
Door opening angle	225 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Storage cabinet

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/949031-8>