

Garant**Garment locker with rotary catch, Number of compartments: 12****Order data**

Order number	949032 12
GTIN	4069515040488
Item class	91G

Description**Version:**

The body of the garment locker has plastic slides in the base frame and a removable plinth panel at the front. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Standard:

DIN 4547

Colour:

Body light grey RAL 7035, doors anthracite RAL 7016, **powder-coated.**

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

usable height of each compartment	370 mm
Depth	520 mm

Data sheet

Height	1850 mm
Sloping roof	no
Special paints available	yes
Weight	114 kg
Nameplate	yes
for padlock	yes
usable depth of each compartment	472 mm
Lock version	Rotary catch
Cabinet fronts	Plain sheet metal swing door
Ventilation slots in the back wall	yes
usable width of each compartment	342 mm
Standard	DIN 4547
Support cabinet version	Aluminium feet
Number of compartments	12
Width	1200 mm
for padlock with shackle Ø up to	6 mm
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Storage cabinet

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/949032-12>