

Garant**Garment locker with rotary catch, Number of compartments: 2****Order data**

Order number	949022 2
GTIN	4069515040518
Item class	91G

Description**Version:**

The body of the garment locker has plastic slides in the base frame and a removable plinth panel at the front. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Each fitted internally with 1 storage shelf (load capacity 40 kg).

Hanger rail with 3 hooks per compartment.

Standard:

DIN 4547

Colour:

Body light grey RAL 7035, doors anthracite RAL 7016, **powder-coated.**

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Number of clothes rails	1
-------------------------	---

Data sheet

Special paints available	yes
Number of compartments	2
usable width of each compartment	342 mm
usable depth of each compartment	472 mm
Width	800 mm
Depth	520 mm
Number of fixed shelves	1
Nameplate	yes
Sloping roof	no
suitable for integral helmets	yes
for padlock	yes
for padlock with shackle Ø up to	6 mm
Support cabinet version	Aluminium feet
Ventilation slots in the door	no
Cabinet fronts	Plain sheet metal swing door
usable height of each clothing compartment	1188 mm
Lock version	Rotary catch
usable height of each hat compartment	370 mm
Weight	68 kg
Ventilation slots in the back wall	yes
Standard	DIN 4547
Height	1850 mm
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Garment locker

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/949022-2>

