

Garant**Garment locker with rotary catch, Number of compartments: 4****Order data**

Order number	949026 4
GTIN	4069515040556
Item class	91G

Description**Version:**

The body of the garment locker has plastic slides in the base frame and a removable plinth panel at the front. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Hanger rail with 3 hooks per compartment.

Standard:

DIN 4547

Colour:

Body light grey RAL 7035, doors anthracite RAL 7016, **powder-coated.**

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	68 kg
for padlock	yes

Data sheet

Standard	DIN 4547
Ventilation slots in the back wall	yes
Height	1850 mm
Special paints available	yes
Ventilation slots in the door	no
Number of clothes rails	1
Lock version	Rotary catch
Sloping roof	no
for padlock with shackle Ø up to	6 mm
usable height of each compartment	780 mm
usable depth of each compartment	472 mm
Width	800 mm
Cabinet fronts	Plain sheet metal swing door
Nameplate	yes
Support cabinet version	Aluminium feet
Number of compartments	4
suitable for integral helmets	yes
Depth	520 mm
usable width of each compartment	342 mm
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Garment locker

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/949026-4>