

Garant**Garment locker with cylinder lock, Number of compartments: 4****Order data**

Order number	949025 4
GTIN	4069515040532
Item class	91G

Description**Version:**

The body of the garment locker has plastic slides in the base frame and a removable plinth panel at the front. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With high quality cylinder lock in the slide handle.

Hanger rail with 3 hooks per compartment.

Standard:

DIN 4547

Colour:

Body light grey RAL 7035, doors anthracite RAL 7016, **powder-coated.**

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Nameplate	yes
Weight	68 kg

Data sheet

Width	800 mm
suitable for integral helmets	yes
Lock version	Cylinder lock
Number of clothes rails	1
Height	1850 mm
Cabinet fronts	Plain sheet metal swing door
usable height of each compartment	780 mm
usable depth of each compartment	472 mm
Support cabinet version	Aluminium feet
Depth	520 mm
Ventilation slots in the back wall	yes
Sloping roof	no
Special paints available	yes
Number of compartments	4
usable width of each compartment	342 mm
Ventilation slots in the door	no
Standard	DIN 4547
Material thickness	0.9 mm
Door opening angle	225 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Garment locker

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/949025-4>