

**ER clamping nut, for ER: 20****Order data**

Order number	309585 20
GTIN	4069515040587
Item class	32Z

Description**Version:**

Thread and taper ground in a single setup for highest concentricity. **With hexagon** 25 AF.

Suitable for:

All standard ER collet chucks.

Optional extras:

ER clamping wrenches, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

External Ø D	34 mm
Thread	M25x1.5
Overall length L	19.5 mm
maximum tightening torque	110 Nm
Standard	DIN 6499 D

Type of product

Clamping nut