

**ER clamping nut, for ER: 25****Order data**

Order number	309585 25
GTIN	4069515040594
Item class	32Z

Description**Version:**

Thread and taper ground in a single setup for highest concentricity. **With slots.**

Suitable for:

All standard ER collet chucks.

Optional extras:

ER clamping wrenches, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

External Ø D	42 mm
Thread	M32x1.5
maximum tightening torque	140 Nm
Overall length L	21 mm

Data sheet

Standard	DIN 6499 D
Type of product	Clamping nut