

**ER clamping nut, for ER: 40****Order data**

Order number	309585 40
GTIN	4069515040617
Item class	32Z

Description**Version:**

Thread and taper ground in a single setup for highest concentricity. **With slots.**

Suitable for:

All standard ER collet chucks.

Optional extras:

ER clamping wrenches, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

maximum tightening torque	240 Nm
External Ø D	63 mm
Thread	M50x1.5
Overall length L	26 mm

Data sheet

Standard	DIN 6499 D
Type of product	Clamping nut