

REGO-FIX▲

**ER clamping nut for sealing rings, for ER: 16****Order data**

|              |               |
|--------------|---------------|
| Order number | 309616 16     |
| GTIN         | 2050002087545 |
| Item class   | 39Z           |

**Description****Version:**

Thread and taper ground in a single setup for highest concentricity.

Nut coated for: lower friction and **increased clamping force** coupled with high wear resistance and corrosion resistance. **With hexagon** 25 AF.

**Suitable for:**

All standard ER collet chucks.

**Optional extras:**

ER clamping wrenches, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Sealing rings No. 309622; 309624; 309628; 309632.

**Note:**

Collet chuck and clamping nut are balanced separately!

**Technical description**

|                           |         |
|---------------------------|---------|
| maximum tightening torque | 80 Nm   |
| External Ø D              | 28 mm   |
| Thread                    | M22x1.5 |

## Data sheet

|                  |              |
|------------------|--------------|
| Overall length L | 22.5 mm      |
| Standard         | DIN 6499 D   |
| Type of product  | Clamping nut |