

REGO-FIX▲

ER clamping nut for sealing rings, for ER: 32



Order data

Order number	309616 32
GTIN	2050002087576
Item class	39Z

Description

Version:

Thread and taper ground in a single setup for highest concentricity.

Nut coated for: lower friction and **increased clamping force** coupled with high wear resistance and corrosion resistance. **With slots.**

Suitable for:

All standard ER collet chucks.

Optional extras:

ER clamping wrenches, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Sealing rings No. 309622; 309624; 309628; 309632.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

Thread	M40x1.5
External Ø D	50 mm
maximum tightening torque	180 Nm

Data sheet

Overall length L	27.5 mm
Standard	DIN 6499 D
Type of product	Clamping nut