

REGO-FIX▲

ER clamping nut for sealing rings, for ER: 40**Order data**

Order number	309616 40
GTIN	2050002087583
Item class	39Z

Description**Version:**

Thread and taper ground in a single setup for highest concentricity.

Nut coated for: lower friction and **increased clamping force** coupled with high wear resistance and corrosion resistance. **With slots.**

Suitable for:

All standard ER collet chucks.

Optional extras:

ER clamping wrenches, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Sealing rings No. 309622; 309624; 309628; 309632.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

External Ø D	63 mm
Overall length L	30.5 mm
Thread	M50x1.5

Data sheet

maximum tightening torque	240 Nm
Standard	DIN 6499 D
Type of product	Clamping nut