

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 16/11 mm

Order data

Order number	260922 16/11
GTIN	4045197653444
Item class	21T

Technical description

Insert size	11 mm
suitable indexable insert	TC.. 1102..
Centre offset L_3	11 mm
Pack of insert screws	269028 7
ISO code toolholder	AH16Q STFCCR/L11
Head length L_1	25 mm
Minimum pre-drill $\varnothing D_{\min}$	18 mm
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500