

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	260922 20/11
GTIN	4045197653451
Item class	21T

Technical description

Centre offset L_3	13 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	23 mm
Head length L_1	32 mm
ISO code toolholder	AH20R STFCL/L11
suitable indexable insert	TC.. 1102..
Insert size	11 mm
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500