

Waldmann 

LED desk lamp, Type: 1



Order data

Order number	974272 1
GTIN	4013330127282
Item class	93L

Description

Version:

Energy-efficient LED desk lamp with anodised aluminium arm and plastic lamp head in umbra grey. Infinitely dimmable via control button in the lamp head. With a sturdy aluminium base. With electronic plug transformer, can be connected via CEE mains adapter (German plug, type F) or USB-A.

Colour temperature neutral white 4,000 K.

The lamp incorporates built-in LED bulbs.

The light source can be exchanged by the manufacturer. The operating unit can be replaced by the end user.

Working duration: > 50,000 hours.

Connection values: 5 V (USB-A), 100 – 240 V AC (CEE mains adapter).

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Technical description

IP Index of Protection	IP 20
Type of fastening	Stand base

Data sheet

Dimmable lighting	stepless
Colour temperature	4000 K
Ex-protected	no
Lamp replaceable	yes
Power consumption	4 W
Support arm reach	588 mm
#Plug type, input	F
On/Off switch	yes
Power supply	Mains-powered
Bulb	LED
Number of LEDs	12
Light colour	neutral white
Overall height	670 mm
ATEX zone	None
Support depth	141 mm
Support width	230 mm
Type of product	Desk lamp / workstation lamp