

**atlas®**

**Lace-up boot, black RUNNER 105, S3, EU shoe size: 46**



## Order data

|              |               |
|--------------|---------------|
| Order number | 092013 46     |
| GTIN         | 4043692449326 |
| Item class   | 09B           |

## Description

### Version:

**Sporty, modern safety shoe from the RUNNER series** with high flexibility.

- **Permanent, active moisture regulation thanks to the aktiv-X functional lining.**
- **Metal-free penetration resistance with XP® midsole.**
- **Steel toecap.**
- **MPU® REBOUND SYSTEM, pressure-relieving insole and responsive sole technology.**
- **clima-stream® concept to maximise the breathability of the shoe.**
- **SPORTY sole system with slats for natural rolling behaviour and very good cushioning in the heel area.**
- **ESD security.**
- **Water-repellent micro-fibre upper.**
- **Lace-up boots with laces.**

### Standard:

EN ISO 20345:2011 S3 SRC

## Technical description

|                                |       |
|--------------------------------|-------|
| EU shoe size                   | 46    |
| Material of protective toe-cap | Steel |

## Data sheet

|                              |                                                    |
|------------------------------|----------------------------------------------------|
| Standard                     | Inlay type-tested according to DGUV regulation 191 |
| Gender                       | Gentlemen's                                        |
| Colour                       | black                                              |
| Protection class             | S3                                                 |
| Series                       | RUNNER                                             |
| Puncture resistance          | Textile                                            |
| electrostatic characteristic | EGB/ESD                                            |
| Characteristic of the sole   | Rebound sole                                       |
| Type of product              | Safety boots                                       |