

atlas®

Lace-up boot, black FLASH 6805 XP®, S3, EU shoe size: 38



Order data

Order number	092021 38
GTIN	4043692430591
Item class	09B

Description

Version:

Dynamic FLASH safety shoe with particularly air-permeable, water-repellent upper and seamless front. High return of energy due to INNOFLEX system and dynamic motion support. Ideal for hard industrial floors. Width 10. Multi-width system available.

- **Sportline upper.**
- **Permanent, active moisture regulation thanks to the aktiv-X functional lining.**
- **Metal-free penetration resistance with XP® midsole.**
- **Aluminium toecap.**
- **MPU® REBOUND SYSTEM, pressure-relieving insole and responsive sole technology.**
- **MPU® INNOFLEX sole system with flex grooves for natural rolling behaviour and cloud zone in the heel area to absorb high impact forces.**
- **ESD security.**

Lace-up boots with laces.

Standard:

EN ISO 20345:2011 S3 SRC

Technical description

Colour	black
--------	-------

Data sheet

Standard	Inlay type-tested according to DGUV regulation 191
EU shoe size	38
Series	FLASH
Puncture resistance	Textile
Material of protective toe-cap	Aluminium
Protection class	S3
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Rebound sole
Type of product	Safety boots