

atlas[®]

Lace-up boot, black FLASH 6905 XP[®] BOA, S3, EU shoe size: 40



Order data

Order number	092023 40
GTIN	4043692441405
Item class	09B

Description

Version:

Dynamic FLASH safety shoe with particularly air-permeable, water-repellent upper and seamless front. High return of energy due to INNOFLEX system and dynamic motion support. Ideal for hard industrial floors. Width 10. Multi-width system available.

- **Sportline upper.**
- **Permanent, active moisture regulation thanks to the aktiv-X functional lining.**
- **Metal-free penetration resistance with XP[®] midsole.**
- **Aluminium toecap.**
- **MPU[®] REBOUND SYSTEM, pressure-relieving insole and responsive sole technology.**
- **MPU[®] INNOFLEX sole system with flex grooves for natural rolling behaviour and cloud zone in the heel area to absorb high impact forces.**
- **ESD security.**

Lace-up boots with BOA closure system.

Standard:

EN ISO 20345:2011 S3 SRC

Technical description

Gender	Gentlemen's
--------	-------------

Data sheet

Characteristics	Rotary closure
Standard	Inlay type-tested according to DGUV regulation 191
EU shoe size	40
Puncture resistance	Textile
Material of protective toe-cap	Aluminium
Colour	black
Series	FLASH
Protection class	S3
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Rebound sole
Type of product	Safety boots