

atlas[®]**Sandals black FLASH 1605 XP[®], S1P, EU shoe size: 44**

Order data

Order number	092024 44
GTIN	4043692376714
Item class	09B

Description

Version:

FLASH safety shoe with high-tech upper wraps precisely around the foot and guarantees the wearer an unmistakable sense of comfort. High return of energy due to INNOFLEX system and dynamic motion support. Ideal for hard industrial floors. Width 10. Multi-width system available.

- **MESH upper.**
- **Permanent, active moisture regulation thanks to the aktiv-X functional lining.**
- **Metal-free penetration resistance with XP[®] midsole.**
- **Aluminium toecap.**
- **MPU[®] REBOUND SYSTEM, pressure-relieving insole and responsive sole technology.**
- **MPU[®] INNOFLEX sole system with flex grooves for natural rolling behaviour and cloud zone in the heel area to absorb high impact forces.**
- **clima-stream[®] concept to maximise the breathability of the shoe.**
- **ESD security.**

Sandals with hook-and-loop fastener.

Standard:

EN ISO 20345:2011 S1P SRC

Technical description

Material of protective toe-cap	Aluminium
Colour	black

Data sheet

Gender	Gentlemen's
Standard	Inlay type-tested according to DGUV regulation 191
Protection class	S1P
Series	FLASH
EU shoe size	44
Puncture resistance	Textile
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Rebound sole
Type of product	Safety sandals