

atlas®

Lace-up boot, black FLASH 6905 XP® BOA, S3, EU shoe size: 43



Order data

Order number	092023 43
GTIN	4043692441436
Item class	09B

Description

Version:

Dynamic FLASH safety shoe with particularly air-permeable, water-repellent upper and seamless front. High return of energy due to INNOFLEX system and dynamic motion support. Ideal for hard industrial floors. Width 10. Multi-width system available.

- **Sportline upper.**
- **Permanent, active moisture regulation thanks to the aktiv-X functional lining.**
- **Metal-free penetration resistance with XP® midsole.**
- **Aluminium toecap.**
- **MPU® REBOUND SYSTEM, pressure-relieving insole and responsive sole technology.**
- **MPU® INNOFLEX sole system with flex grooves for natural rolling behaviour and cloud zone in the heel area to absorb high impact forces.**
- **ESD security.**

Lace-up boots with BOA closure system.

Standard:

EN ISO 20345:2011 S3 SRC

Technical description

Protection class	S3
------------------	----

Data sheet

Colour	black
EU shoe size	43
Characteristics	Rotary closure
Puncture resistance	Textile
Series	FLASH
Material of protective toe-cap	Aluminium
Gender	Gentlemen's
Standard	Inlay type-tested according to DGUV regulation 191
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Rebound sole
Type of product	Safety boots