

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 25/16mm

Order data

Order number	260923 25/16
GTIN	4045197653512
Item class	21T

Technical description

Insert size	16 mm
Minimum pre-drill $\varnothing D_{\min}$	28 mm
Head length L_1	40 mm
Pack of insert screws	269028 8
ISO code toolholder	AH25R STFCL16
Centre offset L_3	17 mm
suitable indexable insert	TC.. 16T3..
Overall length L	200 mm
Clamping height L_2	23 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

Set of insert screws Type 8

269028 8

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500