

Garant**Mini-boring bar, carbide, right-hand, Overhang L1 / insert size d: 64/8mm****Order data**

Order number	270006 64/8
GTIN	64045197569
Item class	21V

Description**Version:**

Low-vibration carbide shank with soldered steel head and hardened insert seat.

- **Carbide insert screwed on to the end face, positive force transmission due to end face serrations.**
- **Insert change is very easy to perform.**

Note:

Only for boring and chamfering!

Technical description

Insert size	08 mm
Insert screw	279815 11
Overall length L	130 mm
Clamping height L ₂	11.5 mm
Shank Ø D _s	12 mm
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

Accessories

Clamping screw Type 11	279815 11
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500