

LOCTITE.**Flat gasket sealant, 50 ml, Manufacturer ID: 574**

Order data

Order number	083331 574
GTIN	4058093008973
Item class	04L

Description

Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

Application:

For torsion-resistant metal flanges.

Note:

Before applying sealant, clean the surfaces with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Labelling of hazardous substances	GHS07: Exclamation mark
Manufacturer's designation	LOCTITE 574
Functional strength to	6 h

Suitable for application area	Liquid gasketing
Working life after date of manufacture	24 mo
Capacity	50 ml
Characteristics	oil-resistant
Characteristics	water-resistant
Characteristics	glycol-resistant
Characteristics	fluorescent under UV light
Storage temperature	8 - 21 °C
Suitable for material	Metal
minimum break-away torque	6 Nm
Dynamic viscosity	23000 mPas
Flashpoint	93.3 °C
Chemical basis	Dimethacrylate ester
Shape	paste
Operating temperature range	-55 - 150 °C
Touch dry after	30 min
Colour	orange
Maximum gap size	0.25 mm
Strength class	medium strength
Density	1.15 g/cm ³
Product name attribute	50 ml
Type of product	Sealant