

atlas[®]**Shoe, black FLASH 3305 XP[®] BOA, S1P, EU shoe size: 48**

Order data

Order number	092026 48
GTIN	4043692451022
Item class	09B

Description

Version:

FLASH safety shoe with high-tech upper wraps precisely around the foot and guarantees the wearer an unmistakable sense of comfort. High return of energy due to INNOFLEX system and dynamic motion support. Ideal for hard industrial floors. Width 10. Multi-width system available.

- **MESH upper.**
- **Permanent, active moisture regulation thanks to the aktiv-X functional lining.**
- **Metal-free penetration resistance with XP[®] midsole.**
- **Aluminium toecap.**
- **MPU[®] REBOUND SYSTEM, pressure-relieving insole and responsive sole technology.**
- **MPU[®] INNOFLEX sole system with flex grooves for natural rolling behaviour and cloud zone in the heel area to absorb high impact forces.**
- **clima-stream[®] concept to maximise the breathability of the shoe.**
- **ESD security.**

Shoe with BOA closure system.

Standard:

EN ISO 20345:2011 S1P SRC

Technical description

EU shoe size	48
Series	FLASH

Data sheet

Protection class	S1P
Gender	Gentlemen's
Material of protective toe-cap	Aluminium
Standard	Inlay type-tested according to DGUV regulation 191
Puncture resistance	Textile
Characteristics	Rotary closure
Colour	black
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Rebound sole
Type of product	Safety shoes