

**uvex**

**Shoe, black/red uvex 1 x-craft, S3L, EU shoe size: 44**



## Order data

|              |               |
|--------------|---------------|
| Order number | 092137 44     |
| GTIN         | 4066853012115 |
| Item class   | 04V           |

## Description

### Version:

**Sporty, ultra-lightweight safety shoe** offers full support and flexibility. High abrasion resistance, optimal protection and breathability. Suitable for wearers allergic to chromium. All sole materials are free of silicones, plasticisers and substances which would impair paint adhesion. Width 11.

- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **Foamed PU overcap to protect the upper material, for significantly longer working life.**
- **Interchangeable comfort insole with moisture transport system and additional fore-foot and heel shock absorption.**
- **Energy-returning, cushioning midsole uvex i-PUREnrj planet with 15% recycled granulate.**
- **ESD security.**
- **Lightweight, breathable micro-velour upper material.**
- **Two-layer PU outer sole with ergonomic sole design bionom x.**

**Safety low-profile shoe** with elastic laces and quick-release fastener.

### Standard:

EN ISO 20345:2022 S3L SR

## Technical description

## Data sheet

|                                |  |
|--------------------------------|--|
| Material of protective toe-cap | Composite  |
| Series                         | uvex 1   |
| Colour                         | black/red  |
| Gender                         | Gentlemen's  |
| EU shoe size                   | 44   |
| Standard                       | Inlay type-tested according to DGUV regulation 191 |
| Puncture resistance            | Textile  |
| Protection class               | S3   |
| electrostatic characteristic   | EGB/ESD  |
| Type of product                | Safety shoes                                       |