



Shoe, black uvex 1 x-craft pro, S1PL, EU shoe size: 50



Order data

Order number	092141 50
GTIN	4066853006732
Item class	04V

Description

Version:

Sporty, ultra-lightweight safety shoe offers full support and flexibility. High abrasion resistance, optimal protection and breathability. Suitable for wearers allergic to chromium. All sole materials are free of silicones, plasticisers and substances which would impair paint adhesion. Width 11.

- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **Foamed PU overcap to protect the upper material, for significantly longer working life.**
- **Interchangeable comfort insole with moisture transport system and additional fore-foot and heel shock absorption.**
- **Energy-returning, cushioning midsole uvex i-PUREnrg planet with 15% recycled granulate.**
- **ESD security.**
- **Breathable and tear-resistant ripstop upper material.**
- **Robust and flexible PUtek upper material in the forefoot area.**
- **Abrasion-resistant uvex x-tended grip planet TPU outer sole.**

Safety low-profile shoe with elastic laces and quick-release fastener.

Standard:

EN ISO 20345:2022 S1PL SR

Technical description

Data sheet

Protection class	S1PL
Standard	Inlay type-tested according to DGUV regulation 191
Colour	black
Series	uvex 1
Puncture resistance	Textile
Material of protective toe-cap	Composite
EU shoe size	50
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes