

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 10/11 mm

Order data

Order number	260923 10/11
GTIN	4045197653475
Item class	21T

Description

Boring bar HSS 10/11 mm Shank $\varnothing D_s$: 10 mm
 ISO code toolholder: AH10K STF/CR/L11
 Setting angle κ : 45°
 suitable indexable insert: TC.. 1102..
 Minimum pre-drill $\varnothing D_{\min}$: 12 mm
 Centre offset L_3 : 7 mm

Technical description

Insert size	11 mm
Centre offset L_3	7 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Head length L_1	16 mm
suitable indexable insert	TC.. 1102..
ISO code toolholder	AH10K STF/CR/L11
Pack of insert screws	269028 7
Overall length L	125 mm
Clamping height L_2	9 mm
Setting angle κ	45°
Shank $\varnothing D_s$	10 mm
Application type	left-hand
Boring depth up to	5×D

Tool material	HSS
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Set of insert screws 10 pieces	269413