

Electrically height-adjustable office desk, Width: 1600mm**Order data**

Order number	974025 1600
GTIN	2050002086319
Item class	91Q

Description**Version:**

Office desk with electric height adjustment using controls. Base of powder-coated bolted steel frame. Table surface mounted by direct bolting on the frame and two asymmetrically arranged profile bearers. The entire leg area of the frame is clear of obstructions, so mobile drawer units up to 560 mm in height can be accommodated under the desk. Speed of travel for height adjustment 38 mm/sec (unloaded). With memory function with 4 memory spaces. Noise level less than 50 dB. Rail with pad for 10 mm height adjustment. Supplied with approach protection by means of resistance measurement. Melamine desk top with décor surface, 25 mm thick.

Standard:

DIN EN 527-1/-2/-3 for the base frame, DIN 60335-1 for electrical safety.

Colour:

Tabletop finish - available in 5 colours: Royal maple, natural oak, light grey, pearl white, metal grey.

Base frame available in 3 colours: Pure white, aluminium silver, metal grey.

Note:

Due to its strong reflection, the table top in metal grey is not recommended.

Technical description

Depth	800 mm
Height adjustment range	650 - 1270 mm
Width	1600 mm

Data sheet

Weight	60 kg
Worktop thickness	25 mm
maximum load capacity	70 kg
Type of height adjustment	electric
Insert thickness	25 mm
Colour selection	Décor: Metal grey, light grey, pearl white, royal maple, natural oak
Colour selection	Metall: Reinweiß, Alusilber, Metallgrau
Type of product	Office desk