

Round conference table, height-adjustable, Type: 1000**Order data**

Order number	974203 1000
GTIN	2050002086371
Item class	91Q

Description**Version:**

Convenient conference table. Round melamine desk top with Ø 1000 mm, 25 mm thick. Round column with star base. Star base made of welded steel stabilisers. Height adjustment range from 720 – 1160 mm. Height adjustment with braked gas pressure spring and manual trigger under the tabletop. Castors with Ø 50 mm for hard and soft floors with locking mechanism on all 4 castors. Load capacity per castor: 50 kg.

Colour:

Tabletop finish - available in 5 colours: Royal maple, natural oak, light grey, pearl white, metal grey.

Base frame available in 3 colours: Pure white, aluminium silver, metal grey.

Technical description

Weight	33 kg
Ø	1000 mm
Worktop thickness	25 mm
Height adjustment range	720 - 1160 mm

Data sheet

Roll Ø	50 mm
Star base Ø	880 mm
Insert thickness	25 mm
Colour selection	Décor: Metal grey, light grey, pearl white, royal maple, natural oak
Colour selection	Metall: Reinweiß, Alusilber, Metallgrau
Type of product	Office desk