

**Shoe, black/white SPEEDY Low ESD, S3S, EU shoe size: 44****Order data**

Order number	092204 44
GTIN	4035877935274
Item class	09P

Description**Version:**

SPEEDY safety shoe that is very comfortable to wear and features reflective elements for good visibility in the dark.

- **Upper made of water-repellent micro-fibre.**
- **Breathable textile lining.**
- **Padded tongue.**
- **JORI ESD black full-size insole.**
- **Rubber/EVA (ethylene-vinyl acetate) sole DYNAMIC, heat-resistant to contact heat.**
- **Abrasion-resistant toe protection.**
- **ESD security.**

Standard:

EN ISO 20345:2022 S3S FO SR HRO

Technical description

Protection class	S3S
Series	SPEEDY
Colour	black/white
Standard	Inlay type-tested according to DGUV regulation 191

Data sheet

Material of protective toe-cap	Composite
EU shoe size	44
Puncture resistance	Textile
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Gender	Gentlemen's
Characteristics	resistant to fuel
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes