

Garant EASYFIX

GARANT easyFix Flex Power, Type: 12V**Order data**

Order number	957520 12V
GTIN	4069515041362
Item class	91F

Description**Version:**

With the GARANT easyFix Flex Power, 18 V rechargeable batteries from all leading power tool manufacturers become individual power banks, so that the rechargeable batteries can be used for different applications: for example, for charging electrical appliances (size USB) or for quick and flexible height adjustment of workbenches (size 12 V). With secure locking on perforated panel systems □ 9×9 mm in a 37-mm grid, can also be used for mobile applications. The Flex Power Station is fully compatible with the CAS rechargeable battery system without the use of an adapter. For rechargeable batteries from other power tool manufacturers, a Scangrip Connector No. 081237 is required (Milwaukee, Fein, Bosch); for other manufacturer rechargeable batteries see eShop at www.hoffmann-group.com under search term "Scangrip Connector". The interface of the Scangrip Connect system provides automatic protection against deep discharge as well as overload protection and temperature monitoring. With on/off switch to disconnect all connected devices from the power supply. Battery level indicator with 5 LED bars (states of charge of 10, 25, 50, 75 and 100% are displayed). With status LED: indicates when active consumer has been connected. Connection via connectors with solder contacts (90 W maximum output power), supplied.

Application tip: By connecting 2 pcs. Flex Power size 12V in series, 24V / 7.5 A (180 W) can be used.

Function:

IP20: No protection against penetration by foreign bodies with Ø < 12 mm, however touching should be avoided, and no protection against water.

Suitable for:

Rechargeable batteries from AEG - AMPSHARE - BERNER - BOSCH - BOSCH GREEN - DEWALT - EINHELL - FEIN - FESTOOL - HAZET - HIKOKI - HILTI - INGERSOLL - MAKITA - METABO - MILWAUKEE - PANASONIC - RIDGID - RUPES - SNAP ON - WÜRTH.

the following connectors:

AEG/RIDGID US No. 03.6158C;

BERNER No. 03.6155C;

BOSCH/AMPSHARE No. 03.6140C;

BOSCH GREEN No. 03.6141C;

DEWALT No. 03.6142C;

EINHELL No. 03.6143C;

FINE No. 03.6144C;

FESTOOL No. 03.6153C;

FLEX No. 03.6145C;

HAZET No. 03.6146C;

HIKOKI No. 03.6147C;

HILTI (21.6 V) No. 03.6157C;

INGERSOLL No. 03.6152C;

MAKITA No. 03.6148C;

MILWAUKEE No. 03.6149;

PANASONIC No. 03.6157;

RIDGID No. 03.6154;

RUPES No. 03.6159;

SNAP-ON No. 03.6151;

WÜRTH No. 03.6150

Supplied with:

Supplied with 2 pcs. GARANT easyFix base plates No. 955820 size 2 for attaching to perforated panels.

Note:

Not suitable for charging rechargeable batteries. Manufacturer rechargeable batteries must be charged using original chargers.

Technical description

outgoing maximum power	90 W
Height	125 mm
Width	185 mm
Series	easyFix
Depth	65 mm
Weight	0.34 kg
IP Index of Protection	IP 20

Type of product

Charger

Suitable products

No Shop URL available for: 957520 12V