

Garant

Garment locker with cylinder lock, Number of compartments: 3



Order data

Order number	949052 3
GTIN	4069515041386
Item class	91G

Description

Version:

Doors with resilient stops. The body has a **sloping top**, plastic slides for the shelf assembly and a **removable plinth panel** at the front. One storage shelf with 2 clothes hooks per compartment. The special construction enables storage of integral helmets, despite a unit width of only 300 mm (design registration applied for).

With high quality cylinder lock in the slide handle.

Standard:

DIN 4547

Colour:

Body light grey RAL 7035, doors anthracite RAL 7016, **powder-coated**.

Note:

- **Lockers are supplied fully assembled.**
- **Padlocks for rotary catch No. 085822 – 085890, as well as DOM padlock No. 085812 size 45; No. 085814 size 45; No. 085816 size 45.**
- **Suitable for locking systems.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Data sheet

Sloping roof	yes
Number of compartments	3
Depth	500 mm
Storage shelf depth	250 mm
Support cabinet version	Base with base fascia
Standard	DIN 4547
Ventilation slots in the door	no
usable width of each hat compartment (integral helmet)	240 - 280 mm
Weight	69.3 kg
Number of clothes rails	1
Nameplate	yes
Base fascia removable	yes
usable width of each clothing compartment	240 mm
usable height of each clothing compartment	1240 mm
Ventilation slots in the back wall	no
Special paints available	yes
Height at the rear	2000 mm
Width	900 mm
suitable for integral helmets	yes
Shelf width	295 mm
Number of fixed shelves	1
usable depth of each clothing compartment	475 mm
Lock version	Cylinder lock
Cabinet fronts	Plain sheet metal swing door
Height at the front	1850 mm
usable depth of each hat compartment	250 mm
usable height of each hat compartment with sloping roof	420 - 480 mm
Door opening angle	225 degrees
Cylinder lock	modular barrel

Data sheet

Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Garment locker

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/949052-3>