

Garant GRIDLINE

Garment lockers with cylinder lock, Number of compartments: 2



Order data

Order number	949072 2
GTIN	4069515041416
Item class	9GF

Description

Version:

Doors with resilient stops. Plastic slides in the base frame. Base frame height 80 mm. Top frame height 40 mm. Top and base flush with the door. Fitted swing doors. The door can easily be converted from right- to left-hinged. With high quality cylinder lock in the slide handle. Internal fitments: With 1 shelf and 3 clothes hooks.

Colour:

Body light grey RAL 7035, doorsanthracite RAL 7016, **powder-coated.**

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	85.3 kg
Width in G	32
Cabinet fronts	Plain sheet metal swing door
Ventilation slots in the back wall	yes

Data sheet

Number of compartments	2
Standard	DIN 4547
usable width of each hat compartment	340 mm
Number of fixed shelves	1
Base fascia removable	no
Depth	500 mm
Height	2000 mm
Sloping roof	no
Lock version	Cylinder lock
Special paints available	yes
usable height of each compartment	1840 mm
usable width of each clothing compartment	340 mm
Width	800 mm
usable height of each hat compartment	370 mm
usable depth of each clothing compartment	450 mm
Depth in G	20
usable height of each clothing compartment	1430 mm
suitable for integral helmets	yes
Ventilation slots in the door	no
Number of clothes rails	1
usable depth of each hat compartment	450 mm
Support cabinet version	Fitted base
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Type of product	Garment locker

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/949072-2>

