


**Boring bar steel, right-hand, Shank  $\varnothing$  / insert size: 20/11mm**

**Order data**

Order number	260930 20/11
GTIN	
Item class	25U

**Description**
**Version:**

Streamlined flutes for improved chip evacuation, reduced tendency to vibrate, stable machining conditions.

**Technical description**

ISO code toolholder	A20R STLCR/L11
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Insert screw	269022 4
Insert size	11 mm
suitable indexable insert	TC.. 1102..
Centre offset $L_3$	11.2 mm
Overall length L	200 mm
Clamping height $L_2$	19 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	20 mm
Application type	right-hand
Boring depth up to	5xD
Standard	DIN 8024
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Insert screw Type 4	269022 4