

**Garant****Mini-boring bar, steel, right-hand, Overhang L1 / insert size d: 12/6mm****Order data**

Order number	270002 12/6
GTIN	4045197558688
Item class	21V

**Description****Version:**

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to perform.

**Technical description**

Insert screw	279815 10
Insert size	06 mm
Head length L <sub>1</sub>	12 mm
Overall length L	80 mm
Clamping height L <sub>2</sub>	15.6 mm
Shank Ø D <sub>s</sub>	16 mm
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

**Accessories**

Clamping screw Type 10	279815 10
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500