



## Internal corner turning tool right-hand similar to DIN 4954, HSS E, Shank Ø: 6Rmm



### Order data

Order number	296400 6R
GTIN	4045197189233
Item class	22E

### Description

**Version:**

All dimensions **welded**.

**Application:**

Universally applicable, medium cutting speeds.

**HSS/E** – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

### Technical description

for bores from Ø	16 mm
Shank Ø	6 mm
Overall length	125 mm
Tool material	HSS E
Type of product	Turning tool