

Garant**Mini-boring bar, steel, right-hand, Overhang L1 / insert size d: 12/8mm****Order data**

Order number	270002 12/8
GTIN	4045197558695
Item class	21V

Description**Version:**

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to perform.

Technical description

Head length L ₁	12 mm
Insert screw	279815 11
Insert size	08 mm
Overall length L	80 mm
Clamping height L ₂	15.6 mm
Shank Ø D _s	16 mm
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

Accessories

Clamping screw Type 11	279815 11
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500