

Garant**Mini-boring bar, carbide, right-hand, Overhang L1 / insert size d: 30/6mm****Order data**

Order number	270006 30/6
GTIN	4045197560025
Item class	21V

Description**Version:**

Low-vibration carbide shank with soldered steel head and hardened insert seat.

- **Carbide insert screwed on to the end face, positive force transmission due to end face serrations.**
- **Insert change is very easy to perform.**

Technical description

Head length L ₁	30 mm
Insert screw	279815 10
Insert size	06 mm
Overall length L	90.5 mm
Clamping height L ₂	11.5 mm
Shank Ø D _s	12 mm
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

Accessories

Clamping screw Type 10	279815 10
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500