



Internal corner turning tool right-hand similar to DIN 4954, HSS E, Shank Ø: 10Rmm



Order data

| | |
|--------------|---------------|
| Order number | 296400 10R |
| GTIN | 4045197189257 |
| Item class | 22E |

Description

Version:

All dimensions **welded**.

Application:

Universally applicable, medium cutting speeds.

HSS/E – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

Technical description

| | |
|------------------|--------------|
| for bores from Ø | 20 mm |
| Shank Ø | 10 mm |
| Overall length | 160 mm |
| Tool material | HSS E |
| Type of product | Turning tool |