

**Side turning tool right-hand similar to DIN 4960, HSS E, Shank square: 12mm****Order data**

Order number	296800 12
GTIN	4045197189974
Item class	22E

Description**Version:**

All dimensions **welded**.

Application:

Universally applicable, medium cutting speeds.

HSS/E – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

Technical description

Shank square	12 mm
Overall length	110 mm
Tool material	HSS E
Type of product	Turning tool