



## Corner turning tool cranked right-hand similar to DIN 4965, HSS E, Shank square: 12mm



### Order data

Order number	296750 12
GTIN	4045197189943
Item class	22E

### Description

**Version:**

All dimensions **welded**.

**Application:**

Universally applicable, medium cutting speeds.

**HSS/E** – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

### Technical description

Shank square	12 mm
Overall length	110 mm
Tool material	HSS E
Type of product	Turning tool