

**Hook turning tool right-hand similar to DIN 4963, HSS E, Shank Ø: 8mm****Order data**

Order number	297120 8
GTIN	4045197190635
Item class	22E

Description**Version:**

All dimensions **welded**.

Application:

Universally applicable, medium cutting speeds.

HSS/E – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

Technical description

Blade width	2 mm
maximum grooving depth t_{\max}	4 mm
for bores from Ø	16 mm
Shank Ø	8 mm
Overall length	140 mm
Tool material	HSS E
Type of product	Turning tool