

**Garant**
**Boring bar steel, right-hand, Shank Ø / insert size: 10/11mm**

**Order data**

Order number	260934 10/11
GTIN	4045197653529
Item class	21T

**Technical description**

Centre offset $L_3$	7 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	13 mm
suitable indexable insert	TC.. 1102..
Head length $L_1$	22.8 mm
ISO code toolholder	A10K STFCCR/L11
Insert size	11 mm
Overall length L	125 mm
Clamping height $L_2$	9 mm
Setting angle $\kappa$	90 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500